

Operating Systems

Windows Installation		UPS Companion	IPP 1.66	IPM 1.67
Windows Server 2019	Standard, Enterprise, Essential	✓	✓	✓
Windows Server 2016	Standard, Enterprise, Essential	✓	✓	✓
Windows Server 2012 R2	Standard, Enterprise, Essential	✓	✓	✓
Windows Server 2012	Standard, Enterprise, Essential	✓	✓	✓
Windows Server 2011	Small business server and Home Server	✓	✓	✓
Windows Server 2008	R2 (Standard, Enterprise, Datacenter)	✓	✓	✓
	Small Business Server	✓	✓	✓
Windows 10	Standard, Pro and Enterprise	✓	✓	✓
Windows 8.1	Standard, Pro and Enterprise	✓	✓	✓
Windows 7	Enterprise, Ultimate, professional, Home Premium, Home Basic	✓	✓	✓
Hyper-V	Server Core 2019; 2016; 2012; 2008	N/A	✓	Not tested

Virtualized Installation		IPP 1.66
VMware	ESXi 6.7 ; 6.5 ; 6.0 (u2) ; 5.5 (u3)	✓
Citrix	XenServer 7.2 ; 7.1 ; 6.5	Not tested
Open Source XEN	Xen 2.6 over RHEL 5	Not tested
	Xen 3.2 on Debian 5	Not tested
KVM	KVM 0.12.1.2 on RHEL 6 and Debian 5	Not tested

Linux		IPP 1.66
RedHat	RHEL 8.0 ; 7.6 ; 7.5	✓
	RHEL 6.10	Not tested
	Fedora Core 28	✓
SUSE	SLES 15	✓
	SLES 12 SP4	✓
	SLES 11 SP4	✓
	SLES 10 SP4	Not tested
	OpenSuseLeap 42.3	Not tested
Debian GNU Linux	Debian 9.4	✓
	Debian 10	Not tested
Ubuntu	18.04 LTS	✓
	19.04	✓

Unix Installation		IPP Unix 1.40
Oracle (Sun)	Solaris 10 & 11 for Sparc	✓
	OpenSolaris 10 for Intel (x86 and x86_64)	✓
HP	HP-UX 11i v2 (11.21) for PA-RISC	✓
	HP-UX 11i v3 (11.31) for PA-RISC	✓
	HP-UX 11i v2 (11.21) for itanium	Not tested
IBM	AIX 6.1 and 7.1 for Power PC	✓

Infrastructure Connectors

VMware		IPM 1.66	IPM 1.67
vCenter or ESXi (stand-alone)	6.7 (only flex for web plugin)	✓	✓
	6.5 ; 6.0	✓	✓
SRM	6.5 to 6.7	✓	✓
vSAN	6.5	✓	✓
	6.7	✓	✓

Microsoft		IPM 1.66	IPM 1.67
SCVMM	2012 R2 ; 2012 ; 2008 R2	X	X
Hyper-V (role & server core)	2019 ; 2016 ; 2012 R2 ; 2008 R2	✓	✓

Nutanix		IPM 1.66	IPM 1.67
Acropolis AHV	AOS 5.1	✓	✓
PRISM central	AOS 5.1	✓	✓

NetApp		IPM 1.66	IPM 1.67
Data ONTAP / Solid fire	9.5 ; 9.1 ; 8.3	Not tested	✓

HPE		IPM 1.66	IPM 1.67
OneView	3.0	✓	✓
OneView	5.0 ; 4.2	✓	✓
ILO	4 or upper	✓	✓

Dell-EMC VxRail		IPM 1.66	IPM 1.67
VxRail Software Manager	4.5.300	X	Not tested
	4.7.000	X	✓