



		UPS Companion	IPP Unix	IPP	IPM
		1.04	1.40	1.61	1.62
Windows Server 2016	Standard, Enterprise, Essential	Not tested	NA	✓	✓
Windows Server 2012 R2	Standard, Enterprise, Essential	✓	NA	✓	✓
Windows Server 2012	Standard, Enterprise, Essential	✓	NA	✓	✓
Windows Server 2011	Small Business Server and Home Server	✓	NA	✓	✓
Windows Server 2008	R1 and R2 (Standard, Enterprise, Datacenter)	✓	NA	✓	✓
	Small Business Server	✓	NA	✓	✓
Windows 10	Standard, Pro and Enterprise	✓	NA	✓	✓
Windows 8.1	Standard, Pro and Enterprise	✓	NA	✓	✓
Windows 7	Enterprise, Ultimate, Professional, Home Premium, Home Basic	✓	NA	✓	✓
RedHat	RHEL 7.4, 7.3, 7.2	NA	NA	✓	NA
	RHEL 6.10	NA	NA	✓	NA
	Fedora Core 28	NA	NA	✓	NA
SUSE	SLES 12 SP3	NA	NA	✓	NA
	SLES 11 SP4	NA	NA	✓	NA
	SLES 10 SP4	NA	NA	Not tested	NA
	OpenSuse 13.2, 13.1 and 12.3	NA	NA	Not tested	NA
Debian GNU Linux	Debian 9.4	NA	NA	✓	NA
Ubuntu	18.04 LTS	NA	NA	✓	NA
	17.10	NA	NA	✓	NA
Oracle (Sun)	Solaris 10 and 11 for Sparc	NA	✓	NA	NA
	OpenSolaris 10 for Intel (x86 and x86_64)	NA	✓	NA	NA
HP	HP-UX 11i v2 (11.21) for PA-RISC	NA	✓	NA	NA
	HP-UX 11i v3 (11.31) for PA-RISC	NA	✓	NA	NA
	HP-UX 11i v3 (11.31) for Itanium	NA	NA	Not tested	NA
IBM	AIX 6.1 and 7.1 for PowerPC	NA	✓	NA	NA
VMware	ESXi 6.5, 6.0 (u2), 5.5 (u3)	NA	NA	✓	NA
HyperV	Server Core 2016	NA	NA	✓	Not tested
	Server Core 2012 R2, 2012	NA	NA	✓	Not tested
	Server Core 2008 R2	NA	NA	✓	Not tested
Citrix	XenServer 7.2 ; 7.1	NA	NA	Not tested	NA
	XenServer 6.5	NA	NA	Not tested	NA
Open Source XEN	Xen 2.6 over RHEL 5	NA	NA	Not tested	NA
	Xen 3.2 on Debian 5	NA	NA	Not tested	NA
KVM	KVM 0.12.1.2 on RHEL 6 and Debian 5	NA	NA	Not tested	NA